
Product datasheet
Characteristics

LAD9V6
Set of power connections, inversing busbar, for 3P reversing contactors assembly, LC1D09-D38 screw clamp terminals



Main

Range of product	TeSys D
Range	TeSys Linergy
Device short name	LAD9
Product or component type	Set of connections
Poles description	3P
Electrical circuit type	Reversing contactor
Range compatibility	TeSys D
Product compatibility	LC1D09 LC1D12 LC1D18 LC1D25 LC1D32 LC1D38

Complementary

Mounting location	Downstream
Connections - terminals	Screw clamp terminals

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	27 g
Package 1 Height	2 cm
Package 1 width	5 cm
Package 1 Length	9.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	294 g
Package 2 Height	9.8 cm
Package 2 width	9.8 cm
Package 2 Length	15 cm
Unit Type of Package 3	S03
Number of Units in Package 3	140
Package 3 Weight	4.6 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months