
# Product data sheet
## Characteristics

# 8903SVO11V02
## lighting contactor, mechanically held, 200 A, 3 pole, open, 120/110V 60/50Hz

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 4,877.00 USD



## Main

| | |
|---|---|
| Product | Mechanically Held Lighting Contactor |
| Type | S |

## Complementary

| | |
|---|---|
| Control Circuit Voltage | 120 V AC 60 Hz<br>110 V AC 50 Hz |
| Current Rating | 200 A |
| Number of Poles | 3P |
| Control Units | No control units |
| Pilot Light | Without pilot light |
| Auxiliary Contacts | Without |
| Other Options | None |
| Electrical connection | Lugs |
| Height | 9.13 in (232 mm) |
| Depth | 6.73 in (171 mm) |
| Width | 5.98 in (152 mm) |

## Environment

| | |
|---|---|
| Enclosure Type | Not rated (open device) surface none |
| Product certifications | UL listed<br>CSA |

## Ordering and shipping details

| | |
|---|---|
| Category | 21324 - 8903 S (NOT S*C) MECH. |
| Discount Schedule | CP1 |
| GTIN | 00785901102502 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---|---|
| Package weight(Lbs) | 10.58 kg (23.33 lb(US)) |
| Returnability | No |
| Country of origin | MX |

## Offer Sustainability

| | |
|---|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov |
| EU RoHS Directive | Compliant<br>EU RoHS Declaration |
| China RoHS Regulation | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information. |

## Contractual warranty

| | |
|---|---|
| Warranty | 18 months |