Product data sheet
Characteristics

9080PF1
Terminal Block Class H or K Fuseholder 1 Pole 250V 30A

Product availability : Stock - Normally stocked in distribution facility

Price* : 30.50 USD



Main

Range	9080FB
Product	Fuse holder

Complementary

Line Rated Current	30 A
System Voltage	<= 250 V AC/DC
Fuse type	H and K
Fuse size	0.5625 x 2 in
Number of poles	1
Electrical connection	Pressure wire clamp
Wire Gauge	AWG 18...AWG 10 (copper or aluminium)
SCCR	10 kA per UL 512
Product certifications	CE UL listed file E40747 CCN IZLT CSA file 70360 class 6225 01
Operating Temperature	-40...257 °F
Mounting Type	Surface mount
Block Material	Thermoplastic block
Wire stripping length	0.4375 in
Terminal Tightening Torque	Screw terminals 25 lbf.in for AWG 14...AWG 10 wire copper
Height	3 in
Width	1.12 in
Depth	1.38 in

Ordering and shipping details

Category	21704 - 9080 K (BLOCKS ONLY)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	CP1
GTIN	00785901567004
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17999999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months