Product data sheet
Characteristics

9422ATDN601
Switch A1 Handle+Mech No Fuse 60A 600Vac

Product availability : Stock - Normally stocked in distribution facility

Price** : 618.20 USD



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Non-fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 hp 200 V AC 15 hp 230 V AC 30 hp 460 V AC 50 hp 575 V AC 10 hp 250 V DC
Handle Type	6 in handle included NEMA 1/3/3R/4 enclosures sheet steel

Environment

Certifications	CSA UL recognized

Ordering and shipping details

Category	21732 - 9422
Discount Schedule	CP1
GTIN	00785901872177
Package weight(Lbs)	3.76 kg (8.3 lb(US))
Returnability	Yes
Country of origin	MX

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months