# Product datasheet
## Characteristics

# DL1BEB
## INCANDESCENT 7W 24VAC/DC BA15D



## Main

| | |
|---|---|
| Range compatibility | Harmony XVP<br>Harmony XVB<br>Harmony XVD |
| Accessory / separate part designation | Incandescent bulb |
| Accessory / separate part type | Incandescent bulb |
| Accessory / separate part category | Lighting accessories |
| Accessory / separate part destination | Beacon and indicator bank |
| [Us] rated supply voltage | 24 V |
| Signalling type | Steady |
| Power dissipation in W | 6.5 W |
| Sale per indivisible quantity | 10 |

## Complementary

| | |
|---|---|
| Bulb base | BA 15d |
| Net weight | 0.09 kg |

## Offer Sustainability

| | |
|---|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Contractual warranty

| | |
|---|---|
| Warranty | 18 months |