Product data sheet
Characteristics

QO200TRNM
Molded Case Switch, QO, 60 A, 1PH, 240 V, 22 kA, A/C, NM

Product availability : Stock - Normally stocked in distribution facility

Price* : 191.00 USD



Main

Product	Switch Weatherproof enclosure
Range	QO
Line Rated Current	60 A
System Voltage	240 V AC

Complementary

Inturrupt Rating	22 kA
Height	8.74 in (222 mm)
Depth	3.9 in (99 mm)
Width	6.5 in (165 mm)
Phase	1 phase
Indoor/Outdoor Use	Enclosed outdoor
For Use With	Air conditioner

Environment

Certifications	UL listed
Ambient Rating	104 °F (40 °C)
NEMA Enclosrue Rating	NEMA 3R

Ordering and shipping details

Category	00044 - A/C DISC & PULL-OUTS
Discount Schedule	DE2A
GTIN	00785901328018
Nbr. of units in pkg.	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package weight(Lbs)	1.9000000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months