Product data sheet
Characteristics

QO340GFI
Mini CB, QO, 40 A, 3P, 208Y/120 V, 10 kA, Plug in, GFI

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 791.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Box lugs

Complementary

Inturrupt Rating	10 kA 208Y/120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 12...AWG 4 aluminium AWG 14...AWG 6 copper
Height	104.65 mm (4.12 in)
Depth	73.91 mm (2.91 in)
Width	57.15 mm (2.25 in)

Environment

Certifications	UL listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00103 - QO 2 POLE GFI CB 40-60A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	DE2A
GTIN	00785901979043
Package weight(Lbs)	0.64 kg (1.41 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months