Product data sheet
Characteristics

QOC24US
Cover, QO, load center, 24 circuits, surface

Product availability : Stock - Normally stocked in distribution facility

Price* : 37.70 USD



Main

Marketing Trade Name	QO
Product	Load Center Cover

Complementary

Cover Type	Surface cover
For Use With	For indoor load center
Surface finish	Painted Gray
Number of circuits	24
Height	20.18 in (512.57 mm)
Maximum Width	14.25 in (361.95 mm)
Maximum Depth	0.7 in (17.78 mm)
Tightening torque	20.36 lbf.in (2.3 N.m) cover

Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901746010
Nbr. of units in pkg.	1
Package weight(Lbs)	6.6 lb(US) (2.99 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.40 in (3.556 cm)

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 width	14.60 in (37.084 cm)
Package 1 Length	21.40 in (54.356 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	162
Package 2 Weight	1051.00 lb(US) (476.725 kg)
Package 2 Height	39.50 in (100.33 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months