

RACK ATS, 230V, 10A, C14 IN, (12) C13 OUT
AP4421

Call for More Information +61 2 9125 8951



- Includes: Mounting hardware, Rack mounting brackets, Serial configuration cable

Output	
Nominal Output Voltage	230V
Overload Protection	No
Maximum Total Current Draw	10
Output Connections	(12) IEC 60320 C13

Input	
Nominal Input Voltage	230V
Input frequency	50/60 Hz
Input Connections	IEC 60320 C14
Load Capacity	2000VA
Maximum Input Current	10A
Maximum Line Current	10A

Physical	
Maximum Height	44MM, 4.4CM
Maximum Width	432MM, 43.2CM
Maximum Depth	236MM, 23.6CM
Rack Height	1U
Net Weight	3.93KG
Shipping weight	5.7KG
Shipping Height	114MM, 11.4CM
Shipping Width	600MM, 60.0CM

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Physical

Shipping Depth	349MM, 34.9CM
Color	Black

Environmental

Operating Temperature	-5 - 45 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-25 - 65 °C
Storage Elevation	0 - 15240meters

Conformance

Approvals	EN 55022 class A, FCC part 15 class A
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.