Product data sheet
Characteristics

QOM125VH
Main breaker, QO, 125A, 2 pole, 120/240 VAC, 22 kA, bolt on mount

Product availability : Stock - Normally stocked in distribution facility

Price* : 468.00 USD



Main

Product	Circuit breaker
Range	QO
Current Rating	125 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Electrical Connection	Lugs
Frame Size	QOM1

Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Wire Size	AWG 4...300 kcmil aluminium/copper
Tightening torque	53.10 lbf.in (6 N.m) 0.01…0.10 in² (4…65 mm²) AWG 12...AWG 2/0)
Maximum Height	5.09 in (129.29 mm)
Depth	5 in (127.00 mm)
Width	3.47 in (88.14 mm)
Load center type	Main breaker
Number of Phases	1 phase
For Use With	QO load center Homeline load center

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00100 - QOM-VH MAIN CB
Discount Schedule	DE3A
GTIN	00785901004042
Nbr. of units in pkg.	1
Package weight(Lbs)	1.26 lb(US) (0.57 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.20 in (10.668 cm)
Package 1 width	4.20 in (10.668 cm)
Package 1 Length	5.30 in (13.462 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months