# Product data sheet
## Characteristics

# NSYPLM3025G
wall-mounting enclosure polyester monobloc IP66 H308xW255xD160mm



has not been replaced. Please contact your customer care center for more information.

## Main

| | |
|---|---|
| Range | Thalassa |
| Product name | Thalassa PLM |
| Device short name | PLM |
| Enclosure type | Multi-purpose |
| Category | Compact enclosure |
| Nominal height | 308 mm |
| Nominal width | 255 mm |
| Nominal depth | 160 mm |
| Enclosure mounting | Wall mounted |
| Device composition | 1 body<br>1 door<br>1 lock |
| Body type | Single piece body |
| Door type | Plain |
| Lock type | 3 mm double-bar lock |

## Complementary

| | |
|---|---|
| Number of locks | 1 |
| Mounting plate description | Without mounting plate |
| Accessibility for operation | Front |
| Removable parts | Door by hinges |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208<br>NEMA classification 13<br>NEMA classification 4X |
| Product certifications | UL |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

| | |
|---|---|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Fire resistance | 960 °C conforming to IEC 62208 |
| Ambient air temperature for storage | -35…90 °C |

## Offer Sustainability

| | |
|---|---|
| Sustainable offer status | Green Premium product |
| REACh Regulation | REACh Declaration |
| REACh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |